

# MATERIAL LIST

TOTAL SHEETS 3

FOR

REVISION 0

TMC MODEL - AX530

TITLE- MN FR SUBASSY

USED ON  
MODEL -

GPT-10KLF

CONSISTS OF  
SUPPORTING LISTS

COMPILED A. KLEIN  
CHECKED \_\_\_\_\_  
ENG APPR \_\_\_\_\_  
FNL APPR J. SABATINO  
ISS DATE 10/25/66

# MATERIAL LIST

AX530  
REV.0

PAGE 1

OF 3

| PART NUMBER   | DESCRIPTION      | USED ON       | QUANTITY | QUANTITY PER UNIT | REFERENCE SYMBOLS | SPECIAL NOTES REFER TO S 1200 |
|---------------|------------------|---------------|----------|-------------------|-------------------|-------------------------------|
| FS102-1       | LOCKSPRING       | MS1590        | 3        |                   |                   | 26                            |
|               |                  | MS1591        | 3        |                   |                   | 26                            |
|               |                  | MS4200        | 5        |                   |                   | 26                            |
|               |                  | MS4207        | 5        | 16*               |                   | 26                            |
| LD1687/MS4207 | SHLD, TOP        | AX530         | 1        | 1*                |                   |                               |
| LD1688/MS4200 | CHAS, PA DECK    | AX530         | 1        | 1*                |                   |                               |
| LWSC3MRN      | WASH., LK, SPLIT | MS1590        | 6        |                   |                   | 26                            |
|               |                  | MS1591        | 6        |                   |                   | 26                            |
|               |                  | MS4200        | 10       |                   |                   | 26                            |
|               |                  | MS4207        | 10       | 32*               |                   | 26                            |
| MS1456        | MN FR, STR       | AX530         | 1        | 1*                |                   |                               |
| MS1530        | BRKT, MTG REL    | MS1456        | 2        | 2*                |                   |                               |
| MS1589        | BRKT, ANG FR LS  | AX530         | 1        | 1*                |                   |                               |
| MS1590        | BRKT, ANG R RSD  | AX530         | 1        | 1*                |                   |                               |
| MS1591        | BRKT, ANG R LSD  | AX530         | 1        | 1*                |                   |                               |
| MS1706        | BRKT, ANG FR RS  | AX530         | 1        | 1*                |                   |                               |
| MS3284-40     | STRAP, CONN      | MS1456        | 2        | 2*                |                   |                               |
| MS4200        | CHAS, PA DECK    | LD1688/MS4200 | 1        | 1*                |                   |                               |
| MS4207        | SHLD, TOP        | LD1687/MS4207 | 1        | 1*                |                   |                               |
| MS4385        | SCREEN DECK      | MS4200        | 2        | 2*                |                   |                               |
| MS4386        | SCREEN TOP       | MS4207        | 1        | 1*                |                   | 26                            |
| MS4898        | BRKT, MTG HV     | MS1456        | 2        | 2*                |                   |                               |

# MATERIAL LIST

AX530  
REV.0

PAGE 2

OF 3

| PART NUMBER | DESCRIPTION      | USED ON   | QUANTITY           | QUANTITY PER UNIT | REFERENCE SYMBOLS | SPECIAL NOTES REFER TO S 1200 |
|-------------|------------------|---|--------------------|-------------------|-------------------|-------------------------------|
| NTH03488N6  | NUT, PLN, HEX    | MS1590<br>MS1591<br>MS4200<br>MS4207  | 6<br>6<br>10<br>10 | 32*               |                   | 26<br>26<br>26<br>26          |
| NT117-31248 | NUT, SELF-LKG    | MS1530<br>MS4898  | 2<br>2             | 4*                |                   |                               |
| NT129-440-6 | NUT, PLN, SPLINE | MS4200  | 4                  | 4*                |                   |                               |
| NT129-832-6 | NUT, PLN, SPLINE | MS4200  | 26                 | 26*               |                   |                               |
| SCFP03488N8 | SCR, MACH        | MS1590<br>MS1591<br>MS4200<br>MS4207  | 6<br>6<br>10<br>10 | 32*               |                   | 26<br>26<br>26<br>26          |
| S404        | IRIDITE, YEL     | MS1456<br>MS1530<br>MS1589<br>MS1590<br>MS1591<br>MS1706<br>MS3284-40<br>MS4200<br>MS4207<br>MS4385<br>MS4386<br>MS4898 |                    | *                 |                   |                               |



# MATERIAL LIST

AX537  
REV.0

PAGE 3

OF 3

| PART NUMBER  | DESCRIPTION    | USED ON | QUANTITY | QUANTITY PER UNIT | REFERENCE SYMBOLS | SPECIAL NOTES REFER TO S 1200 |
|--------------|----------------|---------|----------|-------------------|-------------------|-------------------------------|
| S113         | VARN,FUNG RES. | PX638   |          | *                 |                   |                               |
| TE0102-2     | TERM.,STUD-INS | AX537   | 1        | 1*                |                   |                               |
| TE0111-2     | TERM.,LUG      | AX537   | 1        | 1*                |                   |                               |
| TE0159-32960 | TERM.,LUG-INS  | A-2226  | 1        | 1*                |                   |                               |
| TS106-2      | LIGHT,IND-CLR  | AX537   | 1        | 1*                | XI1004            |                               |
| WA102-4      | WASH.,SHLD-NM  | A-2226  | 2        | 2*                |                   |                               |